

# WTA® HF Alkylation Valves

### www.cranecpe.com

Bellows Sealed Globe Valves provide the highest fugitive emission protection for Hydrofluoric Acid (HF) applications including Alkylation.

# Key features include:

- Superior safety sealing system with multiple walled bellows, gland packing, metal back seat, two-part rising stem, stellite coated, conical shaped piston and seat.
- Compliant with the demanding UOP Specifications for Bellows Sealed Globe Valves used for HF applications.
- 3 The **robust bellows design** offers significant operating and maintenance cost savings.







# **WTA®** HF Alkylation Valves

### **Product Features**

Bellows sealed globe valves with protected bellows and safety gland packing designed for min. 10,000 cycles.

#### **Benefits**

- Less plant downtime due to bellows with longer lifetime and easy as well as quick maintenance on valves due to less parts (<5)</li>
- Low emissions due to TA-Luft approved design
- Design provides higher integrity isolation than other valve designs

### **Typical Applications**

For various media with toxic or aggressive characteristics including HF Alkylation and other HF applications.

### Materials of Construction

- Body made of ASTM A 216 WCB-S16, Monel®, Hastelloy® C276
- Body seat hard-faced with Stellite® 21
- Disc in Hastelloy® C276 hard-faced with Stellite® 6
- Bellows and trim in Monel®, Hastelloy® C276

# **Body Configurations**

- T-type body design
- Globe valve face to face standard
- Gate/Plug valve face to face standard
- Body/bonnet wall thickness exceeds API 602 for additional corrosion resistance

## Size Range

NPS ½" - 12" Other sizes are available upon request

# **Pressure Ratings**

ASME class 300, 600, 800 Other classes are available upon request

#### **End Connections**

Flange design in accordance with ASME B 16.5 and EN 1092-1.

Other classes are available upon request

### **Painting**

Body/bonnet and end flanges painted with HF leakage detection paint.

### Testing

In accordance with UOP and ConocoPhillips requirements including Shell and Helium leak test. WTA® HF Valves exceed API 598 requirements by testing every valve to zero leakage.\*

#### **Automation**

Pneumatic actuated HF valves available with special bellows designed for up to 100,000 cycles.

www.cranecpe.com

<sup>\*</sup> Zero leakage - in accordance with UOP specifications and API 598 standards Hastelloy® is a trademark of Haynes International Inc. Stellite® is a registered trademark of Deloro Stellite.